

TABLE OF CONTENTS

HIGH EAVE (PARAPET)

DI0010 - HIGH EAVE PARAPET with WALL PANEL ABOVE

DI0050 - HIGH EAVE PARAPET with WALL PANEL ABOVE & BELOW

DI0090 - HIGH EAVE PARAPET at MASONRY WALL

DI0130 - HIGH EAVE NON-STRUCTURAL PARAPET




R-PANEL ROOF


DI0010 - HIGH EAVE PARAPET w/ WALL PANEL ABOVE

Download the DWG file by clicking here.

HIGH EAVE LAP & FLASHING BACKER

SLIDE FIELD CUT SECTION FLASHING ENDLAP BACKER ONTO THE LOWER TRIM PIECE. PLACE TAPE MASTIC NEXT TO HEM OF THE BACKER (NOT ON TOP OF HEM). APPLY CONTINUOUS BEAD OF CAULK 1" FROM END OF TRIM DOWN PROFILE OF TRIM. FASTEN LAP WITH STITCH FASTENERS AND POP RIVETS AS SHOWN.





ERECTOR NOTE: INSULATION TIE-OFF SHOWN IS ONE METHOD. MAY REQUIRE DIFFERENT METHOD BASED ON SEQUENCE.H1020 FASTENERS (PURLINS) & H1070 FASTENERS (JOISTS) WITH H2200 INSULATION WASHERS HAVE BEEN SUPPLIED 12" O.C. FOR INSULATION ATTACHMENT

HIGH EAVE PARAPET DETAIL

R-Panel ROOF @ HIGH EAVE PARAPET DETAIL w/ WALL PANEL ABOVE SEE WALL SHEETING ERECTION NOTES FOR WALL PANEL FASTENER LOCATIONS

DI0010

Detailer Notes:

1) INSIDE WALL PANEL CLOSURES ARE ALWAYS PROVIDED AS A STANDARD.

: 12.20.24 (2024-011) **CERTIFIED ERECTION DETAILS** Detail Size (W x H): 1 x 2 Issued




R-PANEL ROOF


DI0050 - HIGH EAVE PARAPET w/ WALL PANEL ABOVE & BELOW

Download the DWG file by clicking here.

HIGH EAVE LAP & FLASHING BACKER

SLIDE FIELD CUT SECTION FLASHING ENDLAP BACKER ONTO THE LOWER TRIM PIECE. PLACE TAPE MASTIC NEXT TO HEM OF THE BACKER (NOT ON TOP OF HEM). APPLY CONTINUOUS BEAD OF CAULK 1" FROM END OF TRIM DOWN PROFILE OF TRIM. FASTEN LAP WITH STITCH FASTENERS AND POP RIVETS AS SHOWN.





ERECTOR NOTE:
INSULATION TIE-OFF SHOWN IS ONE METHOD. MAY REQUIRE DIFFERENT METHOD BASED
ON SEQUENCE.H1020 FASTENERS (PURLINS) & H1070 FASTENERS (JOISTS) WITH H2200
INSULATION WASHERS HAVE BEEN SUPPLIED 12" O.C. FOR INSULATION ATTACHMENT

HIGH EAVE PARAPET DETAIL

R-Panel ROOF @ HIGH EAVE PARAPET DETAIL w/ WALL PANEL ABOVE & BELOW SEE WALL SHEETING ERECTION NOTES FOR WALL PANEL FASTENER LOCATIONS

DI0050

Detailer Notes:

- 1) INSIDE WALL PANEL CLOSURES ARE ALWAYS PROVIDED AS A STANDARD.
- 2) OUTSIDE PANEL CLOSURES ARE OPTIONAL, TURN OFF OUTSIDE CLOSURE LAYER IF NOT REQUIRED.

: 12.20.24 (2024-011) **CERTIFIED ERECTION DETAILS** Detail Size (W x H): 1 x 2 Issued




R-PANEL ROOF


DI0090- HIGH EAVE PARAPET at MASONRY WALL

Download the DWG file by clicking here.

HIGH EAVE LAP & FLASHING BACKER

SLIDE FIELD CUT SECTION FLASHING ENDLAP BACKER ONTO THE LOWER TRIM PIECE. PLACE TAPE MASTIC NEXT TO HEM OF THE BACKER (NOT ON TOP OF HEM). APPLY CONTINUOUS BEAD OF CAULK 1" FROM END OF TRIM DOWN PROFILE OF TRIM. FASTEN LAP WITH STITCH FASTENERS AND POP RIVETS AS SHOWN.





ERECTOR NOTE: INSULATION TIE-OFF SHOWN IS ONE METHOD. MAY REQUIRE DIFFERENT METHOD BASED ON SEQUENCE.H1020 FASTENERS (PURLINS) & H1070 FASTENERS (JOISTS) WITH H2200 INSULATION WASHERS HAVE BEEN SUPPLIED 12" O.C. FOR INSULATION ATTACHMENT

HIGH EAVE PARAPET DETAIL

R-Panel ROOF @ HIGH EAVE PARAPET DETAIL w/ MASONRY WALL

DI0090

Detailer Notes:

1) N/A

: 12.20.24 (2024-011) **CERTIFIED ERECTION DETAILS** Detail Size (W x H): 1 x 2 Issued




R-PANEL ROOF


DI0130 - HIGH EAVE NON-STRUCTURAL PARAPET

Download the DWG file by clicking here.

HIGH EAVE LAP & FLASHING BACKER

SLIDE FIELD CUT SECTION FLASHING ENDLAP BACKER ONTO THE LOWER TRIM PIECE. PLACE TAPE MASTIC NEXT TO HEM OF THE BACKER (NOT ON TOP OF HEM), APPLY CONTINUOUS BEAD OF CAULK 1" FROM END OF TRIM DOWN PROFILE OF TRIM. FASTEN LAP WITH SITCH FASTENERS AND POP RIVETS AS SHOWN.





Detailer Notes:

1) OUTSIDE PANEL CLOSURES ARE OPTIONAL, TURN OFF OUTSIDE CLOSURE LAYER IF NOT REQUIRED.

DI0130

2) MIN AND MAX DIMENSION IS BASED ON ALLOWABLE CANTILEVER FROM DESIGN.

HIGH EAVE NON-STRUCTURAL PARAPET

3) CUSTOM HIGH EAVE TRIM (TRIM-) WILL BE REQUIRED IN ALMOST EVERY NON STRUCTURAL SITUATION ADD OR ADJUST PARTS IN KIT ACCORDINGLY.

Issued: 12.20.24 (2024-011) CERTIFIED ERECTION DETAILS Detail Size (W x H): 1 x 2